


★ **Robustness**



- ★ Min. Spacer Dimension: 250x250 mm
- ★ Max. Spacer Dimension : 2000x2000 mm

	W	L	H	Spacer Thickness
ADF250	1050	1030	3050	6-24 mm

For bigger than 2000x2000 mm spacer applications, machine can be lifted by placing a stand beneath

✔ **Full Automatic Filling**

✔ **Adjustable Working Height**

✔ **Desiccant Filling Procedures Under Your Control**

With our high technology, innovative and ergonomic control panel, all your dehumidifier filling processes take place automatically under your control. Software designed with a user-friendly interface minimizes operator intervention and shorten the process of all desiccant filling processes and offer you the fastest solution.



✔ **Material Tank**

We constantly monitor the level of dehumidifier material in the material tank and provide you with a flow of information about the condition of the material. With the electric heating system, we keep your dehumidifier material warm and ready for use..

✔ **Remote Access**

Remote access feature provides advanced online assistance and troubleshooting



✔ **Fill Rate Detection**

Excess desiccants are collected with our unit to prevent waste. Collected dehumidifiers are re-used for filling.